



SUBMITTAL DATA SHEET

Silent+ Mini Orange

Mini-Split Condensate Pump Kit
Univolt 100-250VAC, 50/60Hz

Project Information:

Job Name: _____

Location: _____

Engineer: _____

Contractor: _____

Distributor: _____

Submitted to: _____

For: Reference Approval Construction

Submitted by: _____

Reference: _____

Submittal Information:

Approval: _____

Date: _____

Construction: _____

Contractor: _____

Distributor: _____

Unit #: _____

Drawing #: _____

Estimated Qty: _____

(Sec. I) Product Specifications:

| | |
|-------------------|--|
| Max. flow | 9.25 US Gallons (35L/h) @ 0m head |
| Max. rec. head | 33ft. / 10m |
| Max. suction lift | 6' / 1.5m |
| Min. dB(A) @ 1m | 16dB(A)* |
| Power supply | 100-250V, 50/60Hz, 0.18A, 2.4W |
| Rated | Continuous |
| Class | II |
| Max. unit output | 40kW / 136,000BTU/h / 11.37 tons |
| Max. ambient temp | 104°F (40°C) |
| IP Protection | IP24 |
| Inlet o/d | 5/8" (16mm) |
| Outlet o/d | 1/4" (Ø6mm) |
| Safety switch | High level safety wires N.C. contacts, 250 VAC, 3A max |
| Self priming | ✓ |

*Assuming solid wall construction with a 2kW unit.
Ensure ALL cleaning chemicals are flushed out of the reservoir after use.

Aspen Pumps Group products are subject to continuous improvements; Aspen Pumps Group reserves the right to modify product design, specifications Pump Selector & Wiring Diagrams Available at & information in this data sheet without notice and without incurring any obligations) malcogrp.com

(Sec. II) Ordering Information:

| | |
|---------------|-------------------------------|
| Product | FP3430/MG |
| Model | Silent+ Mini Orange (5th Gen) |
| Carton Qty | Qty: 1 |
| Carton Weight | 1.7lbs. |

(Sec. III) Carton Contents:

- Silent+ Mini Orange 5th Gen Pump
- Reservoir (incl. filter and lid)
- 5' (1.5m) Plug and Play Cable**
- 5' (1.5m) Clear PVC Tube
- 6" (152mm) Clear Vent Hose
- 8.5" (220mm) Orange Inlet Hose
- Drain connector kit: straight connector and rubber elbow
- Fixing Pad
- Universal Pump Mount
- Quick start guide
- **not backwards compatible


(Fig. I) Product Image:



(Fig. II) Typical Pump Locations:

- Inside linsaset covers
- Inside accessible void
- Above ceiling

Silent+ Mini Orange | 100-250VAC, 50Hz/60Hz



Pump Selector and Wiring Diagrams available at:

